



מגן קפיאה

Dimension (unit: mm)



Specification

Model	Adjusting range (°C)	Factory settings (°C)	The highest temperature of thermo-bulb (°C)	Dimension of thermo-bulb (mm)		Working conditions (°C)
		ON		Length	Diameter	
FRG-LTC	-15~15	5	45	80	8	TS>TB

Note:

1. TS -bulk temperature, TB-the temperature thermo-bulb sense
2. The length of the standard capillary is 1m.

Environment temperature: -20~70 °C

Wire connection: Diameter of wire entrance hole: 15mm

Electrical Ranting

Rated Voltage(V) Rated Current(A)		A.C.110	A.C.220
		20A	10A
Induced current	Full load current	15A	8A
	Instantaneous current	72A	

Contact Form

